



# LED Lamps

## LEDGlobe 10-75W G120 B22 WW 230V\_AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

### Product data

General Information	
Cap-Base	B22
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	827 [CCT of 2700K]
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	1,055 lm
Luminous Efficacy (rated) (Nom)	105 lm/W
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Lamp Current (Nom)	75 mA

Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	50 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	G120


Approval and Application	
Energy Consumption kWh/1000 h	10 kWh
EU RoHS compliant	Yes
EyeComfort	Yes

# LEDLamps

LED Innovations	EyeComfort
<b>Product Data</b>	
Order product name	LEDGlobe 10-75W G120 B22 WW 230V_AU
Full product name	LEDGlobe 10-75W G120 B22 WW 230V_AU
Full product code	871869673240300
Order code	929002442369
Material Nr. (12NC)	929002442369



Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.130 kg
EAN/UPC - Product/Case	8718696732403
Numerator - Packs per outer box	3
EAN/UPC - Case	8719514271715

## Dimensional drawing




Product	D	C
LEDGlobe 10-75W G120 B22 WW 230V_AU	120 mm	168 mm

## Photometric data



General uniform lighting - LEDGlobe 10-75W G120 B22 WW 230V\_AU

Spectral Power Distribution Colour - LEDGlobe 10-75W G120 B22 WW 230V\_AU



Light Distribution Diagram - LEDGlobe 10-75W G120 B22 WW 230V\_AU

# LEDLamps

## Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDGlobe 10-75W G120 B22 WW 230V\_AU

