

Classic filament LEDbulbs

LEDclassic 60W B22 2700K G120 D CL AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Wattage Equivalent	
Cap-Base	B22		60 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	20,000	Warm-up time to 60% light	0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Power Factor (Fraction)	0.7
Lighting Technology	LED	Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	927 [CCT of 2700K]	T-Case Maximum (Nom)	80 °C
Color Code	927 [CCT of 2700K]	Controls and Dimming	
Luminous Flux	806 lm	Dimmable	Only with specific dimmers
Color Designation	Warm White (WW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	2700 K	Bulb Finish	Clear
Luminous Efficacy (rated) (Nom)	134 lm/W	Bulb Material	Glass
Color Consistency	<6	Bulb Shape	G120
Color rendering index (CRI)	90	Net Weight (Piece)	0.165 kg
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Operating and Electrical		Energy Consumption kWh/1000 h	6 kWh
Input Frequency	50 to 60 Hz	EU RoHS compliant	Yes
Power Consumption	6 W		
Lamp Current (Nom)	35 mA		

Classic filament LEDbulbs

Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	LEDclassic 60W B22 2700K G120 D CL AU
Full product name	LEDclassic 60W B22 2700K G120 D CL AU
Full product code	871951438590000
Order code	929003100779



Material Nr. (12NC)	929003100779
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514385900
Numerator - Packs per outer box	3
EAN/UPC - Case	8719514385917

Dimensional drawing




Product	D	C
LEDclassic 60W B22 2700K G120 D CL AU	124 mm	178 mm

Photometric data



General uniform lighting - LEDclassic 60W B22 2700K G120 D CL AU

Light Distribution Diagram - LEDclassic 60W B22 2700K G120 D CL AU



Spectral Power Distribution Colour - LEDclassic 60W B22 2700K G120 D CL AU

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDclassic 60W B22 2700K G120 D CL AU

