



MyCare LED Circular

LED MOD 10W 865

MyCare LED Ceiling Module integrates a LED light source into a module. It is specially designed to replace fluorescent circular tubes working on a G10q fitting. The module offers significant energy savings and a long lifetime.

Product data


General Information	
Cap-Base	- [-]
Nominal lifetime	20,000 hour(s)
Switching Cycle	15,000
Rated Lifetime (Hours)	20,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865 [CCT of 6500K]
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	1,100 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	10 W

Lamp Current (Max)	85 mA
Lamp Current (Min)	85 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	100 mm
Bulb Shape	Others
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance

EyeComfort	Yes
Product Data	
Order product name	LED MOD 10W 865
Full product name	LED MOD 10W 865
Full product code	692234198149400
Order code	929003620509



Material Nr. (12NC)	929003620509
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341981494
Numerator - Packs per outer box	40
EAN/UPC - Case	6922341981500

Dimensional drawing




Product	A1	A2	A3
LED MOD 10W 865	18 mm	126 mm	139 mm

Photometric data





General uniform lighting - LED MOD 10W 865

Light Distribution Diagram - LED MOD 10W 865





Spectral Power Distribution Colour - LED MOD 10W 865

Lifetime




Life Expectancy Diagram - LED MOD 10W 865

Lumen Maintenance Diagram - LED MOD 10W 865



Life Expectancy Diagram - LED MOD 10W 865

Lumen Maintenance Diagram - LED MOD 10W 865



Life Expectancy Diagram - LED MOD 10W 865

