



# Classic filament LEDbulbs

## LED CLA 4W A60 E27 2700K FR UE SRT6

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data


General Information		Wattage Equivalent	
Cap-Base	E27		60 W
Nominal lifetime	50,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	70 °C
Beam Angle (Nom)	300 degree(s)		
Luminous Flux	840 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	No
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	210 lm/W	Bulb Finish	Frosted
Color Consistency	<6	Bulb Material	Glass
Color rendering index (CRI)	80	Bulb Shape	A60
LLMF At End Of Nominal Lifetime (Nom)	70 %	Net Weight (Piece)	0.036 kg
Photobiological safety according to EN 62471	RG1	Approval and Application	
Operating and Electrical		EU RoHS compliant	Yes
Input Frequency	50 to 60 Hz	EyeComfort	Yes
Power Consumption	4 W	LED Innovations	UltraEfficient
Lamp Current (Nom)	43 mA		

# Classic filament LEDbulbs

Ambient temperature range	-20 to +45 °C
<b>Product Data</b>	
Order product name	LED CLA 4W A60 E27 2700K FR UE SRT6
Full product name	LED CLA 4W A60 E27 2700K FR UE SRT6
Full product code	872016939419300
Order code	929003623719


Material Nr. (12NC)	929003623719
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169394193
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169394209

## Dimensional drawing




Product	D	C
LED CLA 4W A60 E27 2700K FR UE SRT6	60 mm	104 mm


## Photometric data



Light Distribution Diagram - LED CLA 4W A60 E27 2700K FR UE SRT6



Spectral Power Distribution Colour - LED CLA 4W A60 E27 2700K FR UE SRT6





General uniform lighting - LED CLA 4W A60 E27 2700K FR UE SRT6

General uniform lighting - LED CLA 4W A60 E27 2700K FR UE SRT6

# Classic filament LEDbulbs

## Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LED CLA 4W A60 E27 2700K FR UE SRT6

