



Classic filament LEDbulbs

LED CLA 7.3W A60 E27 4000K FR UE SRT6

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Wattage Equivalent	
Cap-Base	E27		100 W
Nominal lifetime	50,000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	T-Case Maximum (Nom)	70 °C
Beam Angle (Nom)	300 degree(s)		
Luminous Flux	1,535 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	210 lm/W	Bulb Finish	Frosted
Color Consistency	<6	Bulb Material	Glass
Color rendering index (CRI)	80	Bulb Shape	A60
LLMF At End Of Nominal Lifetime (Nom)	70 %	Net Weight (Piece)	0.039 kg
Photobiological safety according to EN 62471	RG1	Approval and Application	
Operating and Electrical		EU RoHS compliant	Yes
Input Frequency	50 to 60 Hz	EyeComfort	Yes
Power Consumption	7.3 W	LED Innovations	UltraEfficient
Lamp Current (Nom)	71 mA		

Classic filament LEDbulbs

Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	LED CLA 7.3W A60 E27 4000K FR UE SRT6
Full product name	LED CLA 7.3W A60 E27 4000K FR UE SRT6
Full product code	872016939429200



Order code	929003625719
Material Nr. (12NC)	929003625719
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169394292
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169394308

Dimensional drawing




Product	D	C
LED CLA 7.3W A60 E27 4000K FR UE SRT6	60 mm	104 mm

Photometric data



Spectral Power Distribution Colour - LED CLA 7.3W A60 E27 4000K FR UE SRT6


General uniform lighting - LED CLA 7.3W A60 E27 4000K FR UE SRT6



Light Distribution Diagram - LED CLA 7.3W A60 E27 4000K FR UE SRT6

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LED CLA 7.3W A60 E27 4000K FR UE SRT6

