

PHILIPS

Creek Wall Light
60W E27 No-bulb

myGarden

No bulb

White

Water Resistant



15388/31/16



Always light when you come home

Create a charming focal point for your entrance with this white Philips myGarden wall light. It's made from high quality aluminum. With the motion sensor a welcoming pool of light ensures you walk safely into your home.

Feel welcome home with light

- Welcoming & reassuring light
- Easy to set up sensor

Design your garden with light

- Decorative outdoor lighting
- Choose for heritage style
- Choose for outdoor wall lights
- High quality aluminum and superior synthetics

Light up your garden with high quality light

- Energy saving
- Powerful light

Experience outdoor lighting in an easy way

- Weather proof

Highlights

Welcoming & reassuring light

The motion sensor switches on automatically when you come home and informs you when someone arrives.

Easy to set up sensor



A simple set up procedure makes it easy to select when and for how long the automatic sensor switches on the lamp(s).

Decorative outdoor lighting

Outdoor lighting can improve the look of your garden or outside space, illuminating eye-catching features, lighting pathways with style or creating the perfect ambience for those memorable evenings with friends and family. That's why Philips has created myGarden, a range of beautiful decorative outdoor lighting with the flair and functionality to help you make the most of your outdoor space in your own style.

Choose for heritage style

Designed in Europe, this lamp has a unique design signature to help you create a heritage outdoor look.

Choose for outdoor wall lights

Make the most of your outdoor space with this wall light, perfect to mount close to your front door or on your terrace walls.

High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality die-cast aluminum and superior synthetics.

Energy saving



This Philips light conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

Powerful light

This outdoor lamp provides powerful warm white light. A bright pool of light to light up your garden or terrace.

Weather proof



This Philips outdoor lamp is especially designed for humid outdoor environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water, this product is most common and ideal for general outdoor use.

Specifications

Design and finishing

- Color: White
- Material: Aluminium

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Fully weatherproof: Yes
- Motion sensor: Yes

Garden area

- Garden area: Garden & Patio

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Classic
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 0.717 kg
- Height: 28.5 cm
- Length: 17.5 cm
- Width: 20 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Mains power: 50-60 Hz
- LED: No
- Energy class included light source: no bulb included
- Fitting/cap: E27
- Wattage bulb included: -
- Maximum wattage replacement bulb: 60 W
- IP code: IP44
- Class of protection: Class I
- Light source replaceable: Yes
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC - product: 8718291443612
- Net weight: 0.72 kg
- Gross weight: 0.94 kg
- Height: 25.9 cm
- Length: 18.3 cm
- Width: 21.8 cm
- Material number (12NC): 915002791202



Issue date: 2024-06-17
Version: 0.466

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com