

# PHILIPS

## Rock Socket Post

myGarden

Rock side-earthing

Inox

Water Resistant



17108/47/16



## Light up your outdoor life

This outdoor power supply socket is very easy to install. It provides your entire garden with energy, so you can enjoy your outdoor space without limits.

### Designed for your garden

- IP44 - weather proof
- Safe and easy installation
- Bring extra power supply to your garden

# Highlights

## IP44 - weather proof



This Philips outdoor socket is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water.


This outdoor socket is designed with IP44: it is protected against splashing water, ideal for general outdoor use.

## Safe and easy installation



This Philips outdoor socket post is designed for a straightforward installation. You'll find clear guidance about where you can install the product and relevant information about water resistant IP ratings.

## Extra power supply



With this separate power supply socket post you can easily bring extra power to your garden.

# Specifications

## Design and finishing

- Color: Inox
- Material: Stainless Steel
- Housing Color: Inox

## Extra feature/accessory incl.

- Fully weatherproof: Yes

## Garden area

- Garden area: Garden & Patio

## Miscellaneous

- Especially designed for: Garden & Patio
- Style: Contemporary
- Type: Accessories
- Extra Features: Water Resistant

## Product dimensions and weight

- Net weight: 0.937 kg
- Height: 23 cm
- Length: 7.0 cm
- Width: 7.0 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Mains power: 50-60 Hz
- LED: No
- IP code: IP44
- Class of protection: Class I
- Ingress protection code: IP44 | Wire-protected, splash-proof
- Protection class IEC: Safety class I

## Packaging dimensions and weight

- EAN/UPC - product: 8718291455394
- Net weight: 0.94 kg
- Gross weight: 1.05 kg
- Height: 24.5 cm
- Length: 7.9 cm
- Width: 9.7 cm
- Material number (12NC): 915004203801



Issue date: 2024-06-17  
Version: 0.308

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)