

# PHILIPS

Bulb 98W A60M  
E27

LED

3000K

1360lm

15000h

Non-dimmable

8718696823002



## Bright LED lighting with excellent light quality

Philips LED light bulbs provide a cool white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your matted traditional bulbs.

### Energy saving

- Lamp reducing their energy consumption

### Create a warm atmosphere

- A simple LED for everyday use

### Light beyond illumination

- Instant on

# Highlights

## Energy saving

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

## Instant on

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Dimmable: No

## Bulb dimensions

- Height: 11 cm
- Width: 6 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 200 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 1360 lm
- Warm-up time to 60% light: instant full light

## Miscellaneous

- EyeComfort: Yes

## Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 12 W
- Wattage equivalent: 98 W

## Product dimensions and weight

- Length: 11 cm

## Technical specifications

- Frequency: 50–60 Hz

## Packaging dimensions and weight

- EAN/UPC – product: 8718696823002
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 13.7 cm
- Length: 6.1 cm
- Width: 6.1 cm
- Material number (12NC): 929003008107



Issue date: 2024-06-03  
Version: 0.600

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)