



**Lightolier 3D Printed Decorative Pendants, Single Series** allows for thousands of different combinations, tailored to seamlessly match any indoor environment. Create dynamic new decorative styles for your projects by selecting from a variety of polycarbonate materials, visually rich surface textures, unique and creative shapes. Unleash your inner creator and select from the many options these decorative pendants have to offer.

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Fixture

example: 3DP SI CO M WHST HR S CO WH BK E26 FL

Series	Shape	Size	Colors	Texture	Mounting options				Socket	Bulb
					Method	Style	Colors	Cable colors		
<b>3DPSI</b>										
3DP SI Single Series	CO Conical RO Semi Round QR Quarter Round	M Medium L Large	<p><b>Satin colors</b></p> <p>BKST Satin Black BSST Satin Brass BZST Satin Bronze CAPP Satin Cappuccino GYST Satin Grey ROSE Satin Rose SAGE Satin Sage WHST Satin White</p> <p><b>Transparent colors</b></p> <p>CL Clear DIFF Diffuse GYSM Smokey Grey WHTL Translucent white</p>	<p>FLA Layered Fine NLA Layered Natural HR Horizontal Rough VR Vertical Rough WE Wavy Elegant</p>	<p>S Surface</p> <p>T Track</p>	<p>CO Conical canopy DI Disk canopy</p> <p>L Lightolier</p>	<p>WH White mount BK Black mount #### Mounting in Shade Color</p> <p>Note: For options with blank spaces, add color of your choice from the above color options.</p> <p>WH White adapter BK Black adapter</p>	<p>WH White BK Black</p>	<p>E26 E26 socket GU24 GU24 socket (order bulb separately)</p>	<p>N No Bulb FL Clear Filament FR Frosted, 3000K Dim</p>

**Note:** Different colors, textures and custom logo options are available upon request.

### Features

- Customizable:** choose from a wide variety of colors, textures, shapes and styles. Over 500K unique product configurations, 2 million with lamp options.
- Sustainable:** 3D Printed products produce less carbon emissions when compared to traditional, conventional luminaires.
- Local production:** Printed & assembled in Littlestown, PA.
- Quick delivery:** Created on demand and shipped in weeks.

### Electrical

- Dimming:** Dimming possibilities are dependent on LED Lamps.
- Maximum Wattage:** 15W
- Track Mount:** Standard Lightolier track adapter option. Cable length and adapter wiring to be adjusted and wired at the time of install.
- Photometrics:** Dependant on type of lamp used. Check lamp's spec sheet for details. For additional lamp photometric files, please view the 3D Printed Tailored Lighting configurator website (linked on page 1).

### Labels

cULus Listed, 5 year warranty, IP20 & RoHS

### Buy American Act of 1933 (BAA)

This product is manufactured in one of our US factories and, as of the date of this document, this product was considered a commercially available off-the-shelf (COTS) item meeting the requirements of the BAA. This BAA designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Prior to ordering, please visit [www.signify.com/baa](http://www.signify.com/baa) to view a current list of BAA-compliant products to confirm this product's current compliance.



Unleash your inner creator

To configure your custom 3D printed luminaire, scan this QR Code with your smartphone's camera or visit us at: <https://www.3dprinted.lighting.lightolier.com/en/us/Original-Series/>



# Decorative Pendants

## 3D Single

### Dimensions

**COM**  
Single Conical  
Medium



**ROM**  
Semi Round  
Medium




**QRM**  
Quarter Round  
Medium



**COL**  
Single Conical  
Large




**ROL**  
Semi Round  
Large



**QRL**  
Quarter Round  
Large



### FLA Layered Fine



**BKST**  
Satin Black



**BSST**  
Satin Brass



**BZST**  
Satin Bronze



**CAPP**  
Satin Cappuccino




**GYST**  
Satin Grey



**ROSE**  
Satin Rose




**SAGE**  
Satin Sage



**WHST**  
Satin White

### NLA Layered Natural



**BKST**  
Satin Black




**BSST**  
Satin Brass



**BZST**  
Satin Bronze



**CAPP**  
Satin Cappuccino



**GYST**  
Satin Grey



**ROSE**  
Satin Rose



**SAGE**  
Satin Sage




**WHST**  
Satin White


# Decorative Pendants

## 3D Single

### HR Horizontal Rough



### VR Vertical Rough



### WE Wavy Elegant

