

# PHILIPS

Spot 120W R7S R7S

LED

3000K


2000 lm

15000 h

Dimming



8718699773694



## Dimmable linear LED light with a 300-degree beam

This innovative Linear LED is the perfect replacement for halogen R7S bulbs, while far surpassing them in terms of energy efficiency.

### High-quality light

- Cool, energising light

# Highlights

## 3500K [LED Lamps]



This bulb has a colour temperature of 3,500 K providing you with a cool, energising light, perfect for creating an inviting ambiance to host friends or wind down with a book.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional reflector
- Socket: R7s
- Type of glass: Clear
- Lamp Finish: Clear
- Dimmable: Only with specific dimmers
- Bulb material: Plastic

## Lamp dimensions

- Height: 11.8 cm
- Width: 2.9 cm

## Design and finishing

- Material: Plastic

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 3000 K
- Nominal luminous flux: 2000 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 830 | CCT of 3000K

## Miscellaneous

- EyeComfort: No
- Extra Features: Dimmable

## Other characteristics

- Efficacy: 142 lm/W

## Packaging information

- EAN: 8718699773694
- EOC: 871869977369400
- Product title: LED 120W R7S 118mm WH D RF 1PF/12

## Power consumption

- Power factor: 0.8
- Voltage: 220-240 V
- Wattage: 14 W
- Wattage equivalent: 120 W
- Energy efficiency label (EEL): D

## Product dimensions and weight

- Length: 11.8 cm

## Technical specifications

- Frequency: 50-60 Hz
- EPREL registration number: 397582

**Packaging dimensions and weight**  
**[LED 120W R7S 118mm WH D SRT4]**

- EAN/UPC - product: 8718699773694
- Net weight: 0.09 kg
- Gross weight: 0.11 kg
- Height: 14.6 cm
- Length: 3 cm
- Width: 6.3 cm
- Material number (12NC):  
929001353603

**Packaging dimensions and weight**  
**[LED 120W R7S 118mm WH D RF**  
**1PF/12]**

- EAN/UPC - product: 8718699773694
- Net weight: 0.09 kg
- Gross weight: 0.11 kg
- Height: 14.6 cm
- Length: 3 cm
- Width: 6.3 cm
- Material number (12NC):  
929001353650



Issue date: 2024-08-29  
Version: 0.448

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.