

# PHILIPS

Spot 40 W GX53

LED

2700K

500 lm

15000 h



8718699773717



## Durable LED accent lighting with a focused beam

Philips LED standard bulbs provide all-around light perfect for general room lighting.

### High-quality light

- True incandescent-like warm white light

# Highlights

## Incandescent-like warm white



This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2,700 K light is ideal for home lighting design

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: GX53
- Type of glass: Frosted
- Lamp Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

## Lamp dimensions

- Height: 2.6 cm
- Width: 7.5 cm

## Design and finishing

- Material: Plastic

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 500 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Other characteristics

- Efficacy: 90 lm/W

## Packaging information

- EAN: 8718699773717
- EOC: 871869977371700
- Product title: LED 500lm GX53 WW ND SRT4

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 5.5 W
- Energy efficiency label (EEL): F

## Product dimensions and weight

- Length: 2.55 cm

## Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 391874

8718699773717

**Packaging dimensions and weight**

- EAN/UPC - product: 8718699773717
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 12.7 cm
- Length: 7 cm
- Width: 6.3 cm



Issue date: 2025-01-13  
Version: 0.399

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)