

PHILIPS

Reflector 30W R39
E14

LED

2700K

150 lm

15000 h



8718699773755



Durable LED accent lighting with a focused beam

This directional LED lamp provides a focused beam of warm, white light and is an excellent replacement for traditional reflector lamps.

High-quality light

- True incandescent-like warm white light

Highlights

True incandescent-like warm white light



This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2,700 K light is ideal for home lighting design.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E14
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Lamp dimensions

- Height: 6.5 cm
- Width: 3.9 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 150 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Other characteristics

- Efficacy: 83 lm/W

Packaging information

- EAN: 8718699773755
- EOC: 871869977375500
- Product title: LED CLA 30W R39 E14 WW 36D RF ND SRT4

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 1.8 W
- Wattage equivalent: 30 W
- Energy efficiency label (EEL): F

Product dimensions and weight

- Length: 6.5 cm

Rated values

- Rated peak intensity: 250 cd

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 397586

8718699773755

Packaging dimensions and weight

- EAN/UPC - product: 8718699773755
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 12.7 cm
- Length: 4.6 cm
- Width: 6.3 cm



Issue date: 2025-03-18
Version: 0.253

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com