

# PHILIPS

Frosted Glass Bulb 7W  
(Eq.60W) A60 E27

Smart LED

Tunable white

Glass

Easy plug and play

Control with the WiZ app or  
your voice



8719514371965



## Choose from warm or cool white light

With this frosted Philips smart LED A60 Smart bulb, you can get the traditional look of a glass incandescent bulb with smart, warm or cool white light. This bulb is WiZ-connected. Use with your existing Wi-Fi to control with the WiZ app or your voice.

### Easy setup

- Easy plug-and-play. Works with your existing Wi-Fi.

### Smart control

- Control from anywhere with your smartphone.
- Voice control with Google Assistant, Alexa or Siri Shortcuts

### Smart features

- Automate your light with schedules
- Preset well-being features

### Light modes

- Tunable warm to cool white and preset modes
- Customise Scenes with preset dynamic light modes.

### Form factor

- Elegant frosted glass finish

# Highlights

## Easy plug and play

WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

## Control from anywhere

Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

## Voice control

Get hands-free control of your lights by using your voice and Google Assistant, Amazon Alexa or Siri Shortcuts. Use simple voice commands to turn lights on or off, brighten and dim, change colour and set custom light Scenes.

## Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

## Preset well-being features

Use the preset well-being features in the WiZ app to and enjoy the lighting pattern best suited for your circadian rhythm throughout the day. WiZ will provide you bright daylight when you need to get energised and focus, and transition smoothly to soft warm white to help you relax and sleep better.

## Tunable warm to cool white and preset modes

Choose from a wide range of energising cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

## Customised Scenes

Mix different colour and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out at any time with app, WiZmote or voice.

## Frosted glass finish

This bulb has a classic shape with an elegant, frosted glass finish. Perfect for light fixtures with an exposed light, this bulb's design offers a beautiful, glowing halo effect.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: A60
- Socket: E27
- Technology: Smart Wi-Fi
- Type of glass: Frosted
- Dimmable: Only with specific dimmers

## Lamp dimensions

- Height: 10.6 cm
- Weight: 0.042 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 h

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 90
- Colour temperature: 2700-6500 K
- Light Colour Category: Tunable white
- Nominal luminous flux: 806 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 43 mA
- Efficacy: 115 lm/W

## Packaging information

- EAN: 8719514371965
- EOC: 871951437196500
- Product title: PHI WFB 60W A60 E27 927-65 FR TW 1PF/6

#### Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 7 W
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): E

#### Product dimensions and weight

- Length: 10.6 cm

#### Rated values

- Rated lifetime: 15,000 h
- Rated luminous flux: 806 lm
- Rated power: 7 W

#### Service

- Warranty: 2 year(s)

#### Technical specifications

- Frequency: 50–60 Hz
- EPREL Registration Number: 1901117

#### Packaging dimensions and weight

- EAN/UPC – product: 8719514371965
- Net weight: 0.04 kg
- Gross weight: 0.09 kg
- Height: 16 cm
- Length: 7 cm
- Width: 7 cm



Issue date: 2024-11-21  
Version: 0.158

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)