

PHILIPS

Doris Ceiling Light
6W

Outdoor luminaires

2700K

Black

Water Resistant



8719514417878



Create your style with light

The Philips Doris in black adds a modern look to your outdoor space. The stylish light brings high-quality, warm white light to your entrance.

Sustainable light solutions

- Long lifetime up to 15,000 hours

Advanced LED light

- High-quality LED light

Premium quality

- High quality material

Designed for outdoors


- IP54 – weatherproof

High-quality light

- Warm white light 2,700 K

Highlights

Long lifetime up to 15,000 hours



Reliable high-quality LED light lasts up to 15,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

High-quality LED light

These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colours in your garden.


High quality material

This Philips outdoor lamp is made of high-quality materials with superior finishing. This ensures a solid and long-lasting product which is resistant to corrosion and stains in all weather conditions

IP54 – weatherproof

This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP54 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

Warm white light 2,700 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces warm, relaxing light at 2,700 K.

Specifications

Design and finishing

- Colour: Black
- Material: Metal, Plastic

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Anti-rust anti-dust: Yes
- click!FIX mounting: Yes
- compatible with all dimmers: No
- Day-and-night sensor: No
- Defined light beams: Yes
- Dimmable: No
- Dimmable with remote control: No
- FFP - Frustration-Free Pack: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion and day-and-night sensor: No
- Motion sensor: No
- Portable: No
- Remote control included: No
- Rotates freely in any direction: No
- Solar Energy: No
- Tilttable head (up-down): No
- UK plug included: No
- USB charging: No
- Warm White Light: Yes
- Waterproof: Yes
- Centrepiece: No

Garden area

- Garden area: Garden and Patio

Light characteristics

- Colour rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 0.26 kg
- Height: 7 cm
- Length: 22 cm
- Width: 22 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 15,000 h
- Total lumen output fixture: 600
- Light colour: 2700
- LED: Yes
- Energy class included light source: F
- IP code: IP54
- Class of protection: Class I
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC - product: 8719514417878
- Net weight: 0.26 kg
- Gross weight: 0.53 kg
- Height: 28 cm
- Length: 9 cm
- Width: 28 cm
- Material number (12NC): 929003190801



Issue date: 2024-06-21
Version: 0.270

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com