

PHILIPS

Izso Ceiling Light 24 W

Ceiling Lights

2700-6500K

White

Dimmable; Remote Control

8720169196070



Set your desired ambience at your fingertips

With just a few simple clicks on the remote control, the Philips LED All-in-one ceiling light gives you the ultimate flexibility and convenience to personalise your light settings with ease. A comfortable light that's easy on your eyes. Create desired ambience with a light that understands your needs.

Premium quality

- EyeComfort – light that's easy on the eyes

Control

- Tunable – from warm white to cool daylight
- Brightness control with memory function
- 4 pre-set scenes
- A remote control provides easy control for the light settings at up to 10 metres
- Wall-mountable remote-control

Highlights

EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Tunable – from warm white to cool daylight

Tunable lighting lets you change the colour of light to match your mood or activity. Warm white is ideal for relaxation, cool daylight for invigorating focus.

Brightness control with memory function

Memorises the specific brightness levels you prefer.

4 pre-set scenes

Enjoy different ambiances with the convenience of pre-set light scenes for every occasion.

A remote control provides easy control for the light settings at up to 10 metres

Turn lights on or off or change brightness and colour from up to 10 metres away with this remote control.

Wall-mountable remote-control

With the included bracket, you can mount your remote wherever you need an additional switch – no wiring required.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round
- Dimmable: Yes

Design and finishing

- Colour: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable, Remote control

Other characteristics

- Lamp current: 210 mA
- Efficacy: 104 lm/W

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 0.7 kg
- Height: 7 cm
- Length: 38 cm
- Width: 38 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Diameter: 380 mm
- Total lumen output fixture: 2500
- Light colour: 2700–6500
- Mains power: AC 220–240
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC – product: 8720169196070
- Net weight: 0.68 kg
- Gross weight: 1.26 kg
- Height: 8.6 cm
- Length: 46.3 cm
- Width: 46.8 cm



Issue date: 2025-05-13
Version: 0.342

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com