

# PHILIPS

Bulb 60W A60 E27

Smart LED

Tunable white smart bulb

Up to 806 lumens

Easy plug and play

Control with app or voice



8720169302990



## Smart lighting for your daily living

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: A60
- Socket: E27
- Technology: Smart Wi-Fi
- Type of glass: Frosted
- Dimmable: Wireless Dim

## Lamp dimensions

- Height: 11.1 cm
- Weight: 0.05 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 25,000 h

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700-6500 K
- Light Colour Category: Tunable white
- Nominal luminous flux: 806 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 65 mA
- Efficacy: 100 lm/W

## Packaging information

- EAN: 8720169302990
- EOC: 872016930299000
- Product title: PHI WFB 60W A60 E27 827-65 TW 1PF/6

## Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage: 8 W
- Energy efficiency label (EEL): F

## Product dimensions and weight

- Length: 11.1 cm

## Rated values

- Rated lifetime: 25,000 h
- Rated luminous flux: 806 lm
- Rated power: 8 W

## Service

- Warranty: 2 year(s)

## Technical specifications

- Frequency: 50-60 Hz
- EPREL registration number: 1877820
- Flux measurement reference: Sphere

## Packaging dimensions and weight

- EAN/UPC - product: 8720169302990
- Net weight: 0.05 kg
- Gross weight: 0.09 kg
- Height: 16 cm
- Length: 7 cm
- Width: 7 cm
- Material number (12NC): 929003781921



Issue date: 2024-09-18  
Version: 0.102

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)