

**PHILIPS**

Under Cabinet Light  
0.44m

Under Cabinet Lights

3000K

Grey

6922341931628



## Superior light and style

Motion sensor and light up all your space

### Control

- Motion sensor

### Mounting

- Easy to install, safe to use

# Highlights

## Motion sensor

Detects when you enter and leave a room and turns lights off and on to save your electricity bills.

## Easy to install, safe to use

The Philips LED retractable ceiling fan light has passed strict safety testing and includes drop-resistant screws and

a sturdy design alongside other important safety features.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: Grey
- Material: Aluminium

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- On/off switch on wire: No
- Power adapter included: No
- Remote control included: No

## Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 80

## String light/Lightstrip

- Extendibility: No

## Miscellaneous

- Especially designed for: Bedroom, Kitchen, Home Office
- Style: Contemporary
- Type: Under Cabinet Lights
- EyeComfort: No

## Other characteristics

- Lamp current: 10000 mA
- Efficacy: 53 lm/W

## Product dimensions and weight

- Net weight: 0.205 kg
- Height: 0.85 cm
- Length: 44 cm
- Width: 4.15 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lifetime up to: 20,000 hour(s)
- Total lumen output fixture: 160
- Light color: 3000
- Mains power: 5 V
- Fixture dimmable: No
- LED: Yes
- IP code: IP20
- Class of protection: Class III

## Packaging dimensions and weight

- EAN/UPC - product: 6922341931628
- Net weight: 0.25 kg
- Gross weight: 0.3 kg
- Height: 2.3 cm
- Length: 4.5 cm
- Width: 54 cm
- Material number (12NC): 929002698401



Issue date: 2024-06-15  
Version: 0.82

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)