

PHILIPS

Bulb 68W A60S E27

LED

6500K

770lm

15000h

Non-dimmable

8718696822883



Bright LED lighting with excellent light quality

Philips LED light bulbs provide a cool white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your matted traditional bulbs.

Energy saving

- Lamp reducing their energy consumption

Create a warm atmosphere

- A simple LED for everyday use

Light beyond illumination

- Instant on

Highlights

Energy saving

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Instant on

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Bulb dimensions

- Height: 11 cm
- Width: 6 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 200 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 6500 K
- Nominal luminous flux: 910 lm
- Warm-up time to 60% light: instant full light
- Color Code: 965 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 113 lm/W

Packaging information

- EAN: 8718696822883
- EOC: 871869682288300
- Product title: LEDBulb 8W E27 6500K 230V 1CT/12 9 ID

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage: 8 W
- Wattage equivalent: 76 W

Product dimensions and weight

- Length: 11 cm

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718696822883
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 10.7 cm
- Length: 6.1 cm
- Width: 6.1 cm



Issue date: 2025-03-08
Version: 0.531

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com