

# PHILIPS

Bulb 75W A67 E27

LED

6500K

1100lm

15000h

8719514275270



## A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, a long lifetime, and immediate, significant energy savings. With its modern and elegant design, this dimmable bulb is the perfect replacement for your frosted traditional bulbs.

### Light beyond illumination

- 3 hours of emergency lighting

# Highlights

## 3 hours of emergency lighting

You can rely on this emergency bulb for 3 hours of battery powered light.

Ideal for power outages and is automatically recharged from the mains when switched on.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Bulb Finish: Frosted
- Dimmable: No

## Bulb dimensions

- Height: 13.75 cm
- Width: 7.1 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 1100 lm
- Warm-up time to 60% light: instant full light
- Color Code: 865 | CCT of 6500K

## Miscellaneous

- EyeComfort: No

## Other characteristics

- Efficacy: 122 lm/W

## Packaging information

- EAN: 8719514275270
- EOC: 871951427527000
- Product title: LEDBulb BB 9-75W E27 6500K 110-240V A67

## Power consumption

- Power factor: 0.51
- Voltage: 110-240 V
- Wattage: 9 W
- Wattage equivalent: 75 W

## Product dimensions and weight

- Length: 13.75 cm

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8719514275270
- Net weight: 0.13 kg
- Gross weight: 0.15 kg
- Height: 13.8 cm
- Length: 7 cm
- Width: 7 cm



Issue date: 2025-03-08  
Version: 0.114

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)