

PHILIPS

LED Strip kit 4m

Smart LED

Full color

Low Voltage

IP20/Pu-coating



8719514474536



Add a strip of ambience to your space to make it truly cozy

Cut, shape, and reshape this 4m long Indoor Ambience LED Strip as you need it. Colored, dynamic light modes beautify the space under your cabinets or behind furniture, and warm white, ambient light make the mood just right, when it's time to relax.

Easy setup

- Easy plug and play

Smart control

- Control from anywhere with your smartphone
- Go hands-free with voice control

Smart features

- Automate your light with schedules

Light modes

- Millions of colors and dynamic light modes
- Customize Scenes with preset dynamic light modes

Form factor

- Multi-application and simple installation
- Shape lights your way

Highlights

Easy plug and play



WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

Control from anywhere



Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

Go hands-free with voice control



Control your lights with just the sound of your voice, simply enable integration with Google, Alexa or add to your Siri shortcuts.

Automate your light with schedules




Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

Millions of colors and dynamic light modes



Choose from a palette of millions of light colors to create an amazing atmosphere in your home. Enjoy the subtle differences that our dynamic light effects glow your environment.

Customized Scenes




Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, remote or voice.

Multi-application and simple installation



Simply stick to any surface you like – window displays, tray ceilings, work stations and under cabinets. Brightening up and adding Adding accent to your furniture.

Shape lights your way



There's a lot you can do a lot with this 4-meter-long strip of light. Decorate your home by cutting it to suit your space, and tape it on any surface. It even goes around corners.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- On/off switch on wire: Yes
- Power adapter included: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

String light/Lightstrip

- Output Power: 24VDC, 12W Max.

Miscellaneous

- Especially designed for: Functional
- EyeComfort: Yes

Other characteristics

- Lamp current: 73 mA
- Efficacy: 64 lm/W

Power consumption

- Power factor: 0.6
- Voltage: 220-240 V

Product dimensions and weight

- Net weight: 0.225 kg
- Height: 0.3 cm
- Length: 400 cm
- Width: 1 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 840
- Light color: 2700-5000
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 13
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8719514474536
- Net weight: 0.23 kg
- Gross weight: 0.3 kg
- Height: 13 cm
- Length: 5.6 cm
- Width: 14 cm



Issue date: 2024-11-21
Version: 0.76

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com