

# PHILIPS

Indirect light

LIGHTSTRIPS

LED light strip

White

8720169288256



## Durable and bright

Safe and durable low voltage strip provides bright and comfortable light

### Easy to experience

- Easy to install, safe to use

### Safety

- Environment friendly and safe material

### Durability

- Long life span up to 20,000 hours

# Highlights

## Easy to install, safe to use

The Philips LED retractable ceiling fan light has passed strict safety testing and includes drop-resistant screws and a sturdy design alongside other important safety features.

## Environment friendly and safe material

Made from environmentally ethical and child-friendly materials to safeguard your safety and future.

## Long life span up to 20,000 hours

Philips LED technology extends your product's lifetime up to 20,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: White
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- On/off switch on wire: No
- Power adapter included: No
- Remote control included: No

## Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## String light/Lightstrip

- Extendibility: Yes

## Miscellaneous

- Type: Light Strips
- EyeComfort: Yes

## Other characteristics

- Lamp current: 1460 mA

## Product dimensions and weight

- Net weight: 0.305 kg
- Height: 0.14 cm
- Length: 500 cm
- Width: 0.8 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 20,000 hour(s)
- Total lumen output fixture: 900
- Light color: 6500
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: No
- IP code: IP20
- Class of protection: Class II

## Packaging dimensions and weight

- EAN/UPC - product: 8720169288256
- Net weight: 0.31 kg
- Gross weight: 0.41 kg
- Height: 11.5 cm
- Length: 5.1 cm
- Width: 21.6 cm



Issue date: 2025-02-17  
Version: 0.175

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)