

PHILIPS

Recessed spot light

Functional

AstraSpot

White

8718696722336



Superior light and style

LED SpotLight designed for smaller spaces with sharp focus to create ambience

Match your interior

- Expressive and elegant form
- Add vibrancy to your room
- Compact design
- Super slim design

Light effect

- Bright light with uniform distribution
- Bright and focused beam
- Bright and even light

Premium quality

- Durable and impact resistant die-cast aluminum housing
- EyeComfort - light that's easy on the eyes

Material & finishing

- Durable aluminum housing

Durability

- Long life span up to 25,000 hours

Highlights

Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

Add vibrancy to your room

Introduce a splash of character and mark your personality into every room.

Compact design

Compact size allows luminaire to be placed in small spaces.

Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

Bright and even light

Light is clear and distributed evenly around your space in a dependable manner.

Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

Eye comfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Durable aluminum housing

Creates a strong, clean and contemporary style for your space.

Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

Specifications

Design and finishing

- Color: White
- Material: Metal

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional
- EyeComfort: Yes

Product dimensions and weight

- Net weight: 0.331 kg
- Cut out length: 17.8 cm
- Cut out width: 17.8 cm
- Height: 1.8 cm
- Length: 19 cm
- Width: 19 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 190 mm
- Total lumen output fixture: 1800
- Light color: 3000
- Mains power: 220–240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 18
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight [2W LED AstraSpot Integrated GEN 2 (WW)]

- EAN/UPC - product: 8718696722336
- Net weight: 0.01 kg
- Gross weight: 0.02 kg
- Height: 4.5 cm
- Length: 4.5 cm
- Width: 4.5 cm

Packaging dimensions and weight [18w Round Astra Max Plus LED DL(WW)]

- EAN/UPC - product: 8718696722336
- Net weight: 0.31 kg
- Gross weight: 0.4 kg
- Height: 18.9 cm
- Length: 21 cm
- Width: 4.7 cm



Issue date: 2025-02-24
Version: 0.435

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com