

PHILIPS

Downlight

Functional

Full Glow Surface Light

White

8718699698935



Superior light and style

Premium rimless surface downlights with slim design which donot protrude much from the ceiling, provides wider and brighter light output. Ideal for places without false ceiling like balcony, kitchen patio, parking lots, rooms etc

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Bright light with uniform distribution
- Durable synthetic diffuser for uniform light and reduced glare

Durability

- Long life span up to 15,000 hours

Highlights

Suitable for low ceilings
Slim design
Bright light with uniform distribution
 To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Durable synthetic diffuser for uniform light and reduced glare
 Provides a soft glow for relaxation and focus without distracting glare.

Long life span up to 15,000 hours
 Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Design and finishing

- Color: White
- Material: Plastic

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional

Product dimensions and weight

- Net weight: 0.18 kg
- Cut out length: 0 cm
- Cut out width: 0 cm
- Height: 2.9 cm
- Length: 14.5 cm
- Width: 14.5 cm

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 145 mm
- Total lumen output fixture: 1200
- Light color: 6500
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 12
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8718699698935
- Net weight: 0.18 kg
- Gross weight: 0.24 kg
- Height: 14 cm
- Length: 14 cm
- Width: 3.2 cm



Issue date: 2024-11-21
 Version: 0.61

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.