

# PHILIPS

Recessed spot light

Functional

AstraSpot

White

8719514278202



## Superior light and style

LED SpotLight designed for smaller spaces with sharp focus to create ambience

### **Match your interior**

- Expressive and elegant form
- Add vibrancy to your room
- Compact design

### **Light effect**

- Bright and focused beam

# Highlights

## Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

## Add vibrancy to your room

Introduce a splash of character and mark your personality into every room.

## Compact design

Compact size allows luminaire to be placed in small spaces.

## Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

# Specifications

## Design and finishing

- Color: White
- Material: Plastic

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 30 degree(s)
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Functional
- EyeComfort: No

## Product dimensions and weight

- Net weight: 0.025 kg
- Cut out length: 1.6 cm
- Cut out width: 1.6 cm
- Height: 1.6 cm
- Length: 4.2 cm
- Width: 4.2 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 42 mm
- Total lumen output fixture: 100
- Light color: 6500
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 2
- IP code: IP20
- Class of protection: Class II

## Packaging dimensions and weight

- EAN/UPC - product: 8719514278202
- Net weight: 0.01 kg
- Gross weight: 0.02 kg
- Height: 4.5 cm
- Length: 4.5 cm
- Width: 4.5 cm
- Material number (12NC): 929001957303



Issue date: 2024-09-17  
Version: 0.55

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)