

PHILIPS

Downlight

Functional

Prime Neo

White

8719514478190



Durable and bright

Philips premium LED downlights with deep recessed diffuser to help reduce the glare along with thin trim design to blend well with the ceiling

Match your interior

- Super slim design

Light effect

- Bright light with uniform distribution

Premium quality

- EyeComfort – light that's easy on the eyes

Highlights

Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they

meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Specifications

Design and finishing

- Color: White
- Material: Plastic

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional

Product dimensions and weight

- Net weight: 0.09 kg
- Cut out length: 10.6 cm
- Cut out width: 10.6 cm
- Height: 2.6 cm
- Length: 12 cm
- Width: 12 cm

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 120 mm
- Total lumen output fixture: 1000
- Light color: 6500
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 10
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8719514478190
- Net weight: 0.09 kg
- Gross weight: 0.12 kg
- Height: 5 cm
- Length: 15 cm
- Width: 14.5 cm



Issue date: 2025-02-17
Version: 0.64

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com