

# PHILIPS

## 3 Pin Plug Top

Other Wiring Devices

16A

White

913713678601



## Switch to a safer living

Philips Accessories that add safety to your life & design to your Home Décor.

### Easy to use

- Glossy finish

### Safe to use

- FR Grade Polycarbonate Material
- ISI mark

### Longer lifetime

- Brass terminals
- Brass screw

### Durability

- Surge protection upto 2kV
- Superior material quality
- Nickel plated pins

### Convenience

- Convenient gripping

# Highlights

## Glossy finish

Glossy external finish for easy to clean and long lasting finish.

## FR Grade Polycarbonate Material

Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

## ISI mark

ISI mark (tested as per indian standard IS3854).

## Brass terminals

Brass terminal for connection for longer, uninterrupted life.

## Brass screw

Brass screw for longer, carefree operations.

## Surge protection upto 2kV

Surge protection upto 2kV for worry-free usage even during fluctuating electrical grids.

## Superior material quality

Gold plated wire for better connectivity.

## Nickel plated pins

Nickel plated pins provided long life to pin and avoid destruction because of usage.

## Convenient gripping

Serration provided for convenient gripping.

# Specifications

## Design and finishing

- Color: White
- Material: Metal, Plastic

## Durability

- Number of Operation Cycles: 5,000

## Interactivity

- Current (A): 16

## Miscellaneous

- Approval Marks: BIS Certificate

## Other characteristics

- Indicator Type: No Indicator

## Power consumption

- Voltage: 240 V

## Product dimensions and weight

- Height: 6.67 cm
- Length: 5.2 cm
- Width: 5.2 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Frequency: 50 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8718696796399
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 6.7 cm
- Length: 5.2 cm
- Width: 5.2 cm



Issue date: 2025-02-17  
Version: 0.333

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)