

# PHILIPS

SPN Double Door  
Distribution Board

Circuit Breakers

White

913713969601



## Switch to a safer living with wide range of distribution boxes

Philips Distribution Box come with dual tone, metal & plastic; along with detachable glands.

### Easy to use

- Wide range to choose from
- Detachable gland
- Flexible installation
- Side locking on din rail
- Earth link terminal & screw
- Separate neutral terminal

### Pure and elegant design

- Dual tone

### Durability

- Longer life

### Convenience

- Convenient mounting

# Highlights

## Wide range to choose from

Available in 2M, 3M, 4M, 6M, 8M Linear, 8M Square, 12M & 18M size.

## Detachable gland

Front panel easily detachable with glands which makes it easy to use during installation.

## Flexible installation

Adjustable blanks to make different combination more flexible & convenient during installation.

## Side locking on din rail

Side lock available on Din Rail to avoid accidental fall of circuit breakers during installation.

## Earth link terminal & screw

Separate Earth link Terminal & Screw for easy mounting of earthing wires.

## Separate neutral terminal

Separate Neutral link Terminal & Screw for easy mounting of Neutral wires.

## Dual tone

Dual tone finish with Plastic on the corners which flushes with the overall colour and finish.

## Longer life

Best grade powder coating to avoid rusting and good looking surface finish.

## Convenient mounting

Can be mounted either on surface or inside the wall.

# Specifications

## Design and finishing

- Color: White
- Material: Metal

## Interactivity

- Current (A): 63

## Other characteristics

- Installation Type: Din Rail

## Power consumption

- Voltage: 415 V

## Product dimensions and weight

- Length: 45.3 cm
- Width: 41.3 cm
- Depth: 9.5 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Frequency: 50 Hz
- Class of protection: I - earthed

## Packaging dimensions and weight

- EAN/UPC - product: 8718699684167
- Net weight: 5.75 kg
- Gross weight: 5.8 kg
- Height: 9.5 cm
- Length: 45.3 cm
- Width: 41.3 cm



Issue date: 2025-02-17  
Version: 0.330

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)