

PHILIPS

Wall light

Led indoor

3W

Aluminium

Black

220-240 V

919215850324



Express your style with light

Easy to adjust goose neck arm. Long life LED light source. Premium material and finish

Ease of use

- Easy to adjust gooseneck arm

Easy installation

- Easy installation

Light effect

- Provides a bright white light

Sustainable light solutions

- High quality LED light

Beacon of trust


- You can trust what the Philips packaging is saying

Highlights

Easy to focus

Specially designed gooseneck arm allows you to freely adjust the light direction and focus.

Easy installation



No more hassle in installation. Just fix or hang securely on the wall and plug in, now this luminaire is ready to light on.

Superior light quality High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Black
- Material: Metal

Extra feature/accessory incl.

- LED integrated: Yes
- Premium quality material: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Home office & Study
- Style: Functional
- Type: Wall Lights
- EyeComfort: Yes

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Total lumen output fixture: 150
- Bulb technology: LED
- Light color: 2700-6500K
- Mains power: 220-240 V
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- Wattage bulb included: 3W
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8718696538449
- Net weight: 0.22 kg
- Gross weight: 0.27 kg
- Height: 9 cm
- Length: 14 cm
- Width: 13 cm
- Material number (12NC): 919215850324



Issue date: 2024-07-25
Version: 0.380

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com