

PHILIPS

IP44 bathroom
ceiling light

myBathroom

27W; 2300 lumen; In-built LED;

Premium glass for reduced
glare;

Adjustable head with swivel
joint;

Robust metal construction

919215850905



Add the style, enhance the clarity

It takes more than soap and water to keep a person well groomed. Choose this range for a bright and shiny look for yourself and your bathroom. This light provides maximum clarity with minimal glare and is just right for your bathroom with IP44 moisture protection, a premium opal glass housing and chrome mount for a mirror finish

Extra burst of energy for more focus

- Bright light to enhance your work and play

Highlights

High quality of light

Bright light energizes and enhances your work and play. This light can help

you stay focused making tricky tasks simpler.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Chrome
- Material: Metal, Glass

Extra feature/accessory incl.

- 4 light recipes: No
- 5 years warranty on the LED module: No
- Adjustable height: No
- Adjustable spot head: No
- Batteries included: No
- Bi-directional light beams: No
- Candle light effect: No
- Centerpiece: Yes
- Choose your color: No
- Clamp included: Yes
- Color changing (LED): No
- Day-and-night sensor: No
- Defined light beams: No
- Fully weatherproof: No
- Hue bridge included: No
- Hue Switch: No
- Hue Switch Included: No
- LED integrated: Yes
- Perfectly suited for ambiance creation: Yes
- Premium quality material: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bathroom
- Style: Contemporary

Product dimensions and weight

- Height: 9.5 cm
- Height maximum: 9.5 cm
- Length: 50 cm
- Width: 50 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 20,000 hour(s)
- Lamp lifetime up to: 20,000 hour(s)
- Total lumen output fixture: 2300
- Bulb technology: LED
- Light color: warm white
- Mains power: 220-240 V
- LED: Yes
- Built in LED: Yes
- Energy class included light source: built in LED + bulb of class A+
- IP code: IP44

Packaging dimensions and weight

- EAN/UPC - product: 8719514401907
- Net weight: 1.29 kg
- Gross weight: 1.69 kg
- Height: 45 cm
- Length: 44.5 cm
- Width: 11.5 cm



Issue date: 2025-02-17
Version: 0.55

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com