

PHILIPS

LED Integrated
Floor Lamp

myLiving

24W; Warm White; 840 lumen;
In-built LED;

Minimalist design;

With pedal dimming;

Perfect for living room, drawing
room, and bedroom

919215851208



Epitome of beauty

Ebony has been crafted keeping minimalism as the heart of its design language. A clean, clear and uncluttered design like Ebony is surely going to lend serenity to your abode. You can make those corners in your home serene with Ebony floor lamp's soothing light, which comes with pedal dimming (dimming through foot) feature.

Light modes

- Soft warm white light

Highlights

Soft warm white light

Create a cozy atmosphere with warm white light. A smart light that simply adapts to your daily activities

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Black
- Material: Aluminium

Extra feature/accessory incl.

- Adjustable height: No
- Adjustable spot head: No
- Anti rust anti dust: No
- Dimmable: Yes
- Dimmer and on/off switch on article: Yes
- Dimmer on article: Yes
- LED integrated: Yes
- On/off switch on article: Yes
- Perfectly suited for ambiance creation: Yes
- Premium quality material: Yes
- Warm glow dimmable light: Yes
- Warm White Light: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Expressive

Product dimensions and weight

- Net weight: 2.796 kg
- Height: 150 cm
- Length: 24.5 cm
- Width: 24.5 cm
- Height: 59.06 inch
- Length: 9.65 inch
- Width: 9.65 inch

Service

- Warranty: 1 year(s)

Technical specifications

- Total lumen output fixture: 840
- Bulb technology: LED
- Light color: warm white
- Mains power: 220-240 V
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- IP code: IP20
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC - product: 8720169275652
- Net weight: 2.8 kg
- Gross weight: 3.86 kg
- Height: 6.6 cm
- Length: 151.8 cm
- Width: 32.8 cm



Issue date: 2024-11-21
Version: 0.142

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com