



Strip 1 x 9290026971 2700K

1 x 1350 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.00
Service downward 1.00

CIE flux code 46 79 96 100 100

UGRcen (4Hx8H, 0.25H) 25

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)												
	0.80 0.80				0.70 0.70 0.70 0.70				0.50 0.50 0.30 0.30				0.00
	0.50 0.50	0.30 0.10	0.30 0.20	0.10 0.10	0.30 0.10	0.10 0.10	0.10 0.10	0.10 0.10	0.10 0.10	0.10 0.10	0.10 0.10	0.00	
0.60	0.47	0.45	0.47	0.45	0.44	0.37	0.36	0.32	0.36	0.31	0.29		
0.80	0.58	0.55	0.57	0.56	0.54	0.46	0.46	0.41	0.45	0.40	0.38		
1.00	0.67	0.63	0.66	0.64	0.62	0.54	0.53	0.48	0.53	0.48	0.46		
1.25	0.76	0.70	0.74	0.72	0.69	0.62	0.61	0.56	0.60	0.56	0.53		
1.50	0.83	0.75	0.81	0.77	0.74	0.68	0.67	0.62	0.65	0.61	0.59		
2.00	0.93	0.83	0.90	0.86	0.82	0.76	0.75	0.71	0.74	0.70	0.68		
2.50	1.00	0.88	0.97	0.92	0.87	0.82	0.81	0.77	0.79	0.76	0.74		
3.00	1.04	0.91	1.01	0.96	0.90	0.86	0.85	0.81	0.83	0.80	0.78		
4.00	1.10	0.96	1.07	1.00	0.94	0.91	0.89	0.87	0.88	0.86	0.83		
5.00	1.14	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86		

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	11204	10853	10545	10295	10111	9998	9961
50.0	11123	10710	10353	10064	9853	9726	9683
55.0	10936	10453	10040	9711	9473	9329	9282
60.0	10717	10149	9671	9296	9027	8866	8813
65.0	10274	9608	9060	8638	8340	8164	8105
70.0	9671	8882	8255	7783	7457	7265	7203
75.0	8628	7699	6998	6490	6148	5951	5888
80.0	7202	6087	5319	4800	4466	4279	4219
85.0	5023	3669	2933	2502	2249	2115	2073
90.0	212500	1306	678	480	392	352	340

(cd/m²)

2021-08-11