



Strip 1 x 9290026980 3000K

1 x 2400 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00

CIE flux code 46 79 96 100 100

UGRcen (4Hx8H, 0.25H) 27

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80 0.80				0.70 0.70				0.50 0.50				0.30 0.30			
	0.80	0.50	0.30	0.10	0.50	0.20	0.10	0.10	0.30	0.10	0.10	0.10	0.10	0.10	0.10	0.10
0.60	0.47	0.45	0.47	0.45	0.44	0.37	0.36	0.32	0.36	0.31	0.29	0.29	0.29	0.29	0.29	
0.80	0.58	0.55	0.57	0.56	0.54	0.46	0.46	0.41	0.45	0.40	0.38	0.38	0.38	0.38	0.38	
1.00	0.67	0.63	0.66	0.64	0.62	0.54	0.53	0.48	0.53	0.48	0.46	0.46	0.46	0.46	0.46	
1.25	0.76	0.70	0.74	0.72	0.69	0.62	0.61	0.56	0.60	0.56	0.53	0.53	0.53	0.53	0.53	
1.50	0.83	0.75	0.81	0.77	0.74	0.68	0.67	0.62	0.65	0.61	0.59	0.59	0.59	0.59	0.59	
2.00	0.93	0.83	0.90	0.86	0.82	0.76	0.75	0.71	0.74	0.70	0.68	0.68	0.68	0.68	0.68	
2.50	1.00	0.88	0.97	0.92	0.87	0.82	0.81	0.77	0.79	0.76	0.74	0.74	0.74	0.74	0.74	
3.00	1.04	0.91	1.01	0.96	0.90	0.86	0.85	0.81	0.83	0.80	0.78	0.78	0.78	0.78	0.78	
4.00	1.10	0.96	1.07	1.00	0.94	0.91	0.89	0.87	0.88	0.86	0.83	0.83	0.83	0.83	0.83	
5.00	1.14	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86	0.86	0.86	0.86	0.86	

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	19918	19294	18747	18302	17974	17775	17708
50.0	19775	19041	18405	17892	17517	17290	17215
55.0	19441	18583	17849	17264	16841	16586	16501
60.0	19053	18042	17193	16526	16048	15762	15667
65.0	18264	17080	16107	15356	14827	14512	14409
70.0	17193	15790	14675	13837	13256	12916	12805
75.0	15338	13687	12440	11538	10930	10580	10467
80.0	12803	10820	9456	8533	7939	7607	7500
85.0	8932	6525	5216	4450	3999	3760	3686
90.0	378750	2328	1209	856	699	627	606

(cd/m²)

2021-08-11