

PHILIPS

Halogen spot

50 W

GU5.3 cap

Warm white

8711500885791



Superior halogen lighting

Provides bright, sparkling light with superior dimmability. An ideal accent for stylish homes.

Personal scene setting

- Best dimmability to dims and create a cosy atmosphere

Create a cosy atmosphere

- Bright halogen light provides better contrast for more focus
- Bright, sparkling lighting to create your light scene at home

Create a decorative effect

- Accent light that can help create perfect focus on objects

Highlights

Best dimmability

This lamp can be used in combination with all dimmers and will not only turn down the light to 0% but also create a cosy atmosphere as you are used to with your incandescent.

Halogen contrast for focus

With bright halogen light, contrasts get richer, letters become sharper and visibility gets better. Bright light is more relaxing for your eyes for a better focus.

Bright, sparkling light

Clear halogen is a sparkling light, giving beautiful reflections where it shines, and sharp shadows where it doesn't. Philips halogen lamps give decorative light effect to your room, to bring your room to life.

Decorative accent light

This Philips lamp is perfect for home use in stylish rooms where accent lighting is required for a strong focus.

Specifications

Bulb characteristics

- Shape: Spot
- Socket: GU5.3
- Dimmable: Yes

Bulb dimensions

- Height: 51 mm
- Width: 46 mm

Durability

- Average life (at 2.7 hrs/day): 2 year(s)
- Number of switch cycles: 8,000
- Nominal lifetime: 2,000 hour(s)

Light characteristics

- Application: Accent light
- Beam angle: 36 degree(s)
- Color rendering index (CRI): 100
- Color temperature: 2800 K
- Light Color Category: Warm White
- Correlated Color Temperature (Nom): 3000 K

Power consumption

- Voltage: 12 V
- Wattage: 50 W
- Power Consumption: 50 W

Rated values

- Rated lifetime: 2,000 hour(s)

Technical specifications

- Dimmable: Yes
- Cap-Base: GU5.3

Packaging dimensions and weight

- EAN/UPC – product: 8711500885791
- Net weight: 0.03 kg
- Gross weight: 0.04 kg
- Height: 5.6 cm
- Length: 4.6 cm
- Width: 4.6 cm



Issue date: 2025-03-18
Version: 0.581

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com