

# PHILIPS

Bulb 67W A60 B22  
x8

LED

3000K

1150lm

10000h

8720169371026



## A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### **Choose a simple replacement for your old bulbs**

- Similar shape and size as standard incandescent bulb

### **Create the right light for your home**

- A simple LED for everyday use

# Highlights

## Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

## Bulb dimensions

- Height: 10.8 cm
- Width: 6 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 10,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 1150 lm

## Miscellaneous

- EyeComfort: No

## Other characteristics

- Efficacy: 104 lm/W

## Packaging information

- EAN: 8720169371026
- EOC: 872016937102600
- Product title: ESS LEDBulb 11W B22 3000K 230V 8CT/5 AU

## Power consumption

- Power factor: 0.51
- Voltage: AC 220-240 V
- Wattage: 11 W
- Wattage equivalent: 67 W

## Product dimensions and weight

- Length: 10.8 cm

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8720169371026
- Net weight: 0.29 kg
- Gross weight: 0.35 kg
- Height: 16.6 cm
- Length: 6.2 cm
- Width: 24.4 cm



Issue date: 2024-11-21  
Version: 0.44

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)