

# PHILIPS

2P+E Socket & 1 Gang 1  
Way Switch with Grid

Switches & Sockets

LeafStyle

Polycarbonate

Mettalic Black

Set

8719514298910



## High quality switch and socket designed to safely last for years

Philips LeafStyle provides modern design, high safety standard and easy to install switch & socket to your family.

### **Longer lifetime**

- Long life cycles

### **Safety and Durability**

- Shutter protection
- Safety and Durability

### **Easy for use**

- Easy for use, save time and energy

### **Modern Design**

- Modern design, more than a functional part, it is a decoration

# Highlights

## Long life cycles

Switch could ensure 40000 times of operation; socket could ensure 5000 times of operation.

## Shutter protection

Shutter design for most sockets to protect kids.

## Safety and Durability

1. High quality PC for Cover and Base.2. Key metal parts are used with 0.6mm thickness phosphor bronze.3. Pass IEC standard and follow more strict Philips internal design rule.

## Easy for use

1. Smaller module height, which will make installation more easy.2. Quick installation terminal, no need to use screw.

## Modern Design

1. The inspiration of our design is the natural curve of leaf, could be an art decoration for your home.2. Two classic colors -- white and metallic black to match various home styles.

# Specifications

## Design and finishing

- Color: Black
- Material: PC
- Module/Gang: 1 Module
- Socket/connector Type: 2 Pin + E
- Product Range: LeafStyle
- Minimum Installation Box Depth: 34 cm

## Durability

- Number of Operation Cycles: 4,000, 5,000

## Interactivity

- Current (A): 16

## Miscellaneous

- Approval Marks: Philippine standard safety certification mark

## Other characteristics

- Installation Type: Screwed Installation
- Indicator Type: No Indicator
- Switch Function: 1 Way

## Power

- Electrical Load Type: Resistive load, Inductive load, Capacitive load

## Power consumption

- Voltage: 250 V

## Product dimensions and weight

- Length: 12 cm
- Width: 7 cm
- Depth: 3.2 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8719514298910
- Net weight: 0.09 kg
- Gross weight: 0.09 kg
- Height: 3.2 cm
- Length: 12 cm
- Width: 7 cm



Issue date: 2024-11-21  
Version: 0.267

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)