

# PHILIPS

## Bar linear light

Smart LED

Full color

Versatile bar light

Easy plug and play



8719514435155



## Make your tiny spaces light with ambience

If you have a shelf or corner that needs accent lighting, try our Bar light. This slim bar radiates plenty of colors and is easy to fit in small spaces. Simply tilt it on one of its sides to adjust the light angle. Do you prefer a longer light? Connect a second bar to double the effect.

### Easy setup

- Easy plug and play

### Smart control

- Control from anywhere with your smartphone
- Go hands-free with voice control

### Smart features

- Automate your light with schedules

### Light modes

- Millions of colors and dynamic light modes
- Tunable warm to cool white and preset modes
- Customize Scenes with preset dynamic light modes

### Form factor

- Unique and slender design

# Highlights

## Easy plug and play



WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

## Control from anywhere



Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

## Go hands-free with voice control



Control your lights with just the sound of your voice, simply enable integration with Google, Alexa or add to your Siri shortcuts.

## Automate your light with schedules



Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

## Millions of colors and dynamic light modes



Choose from a palette of millions of light colors to create an amazing atmosphere in your home. Enjoy the subtle differences that our dynamic light effects glow your environment.

## Tunable warm to cool white and preset modes



Choose from a wide range of energizing cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

## Customized Scenes



Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, remote or voice.

## Versatile bar light



This lamp is easy to tilt so it can shine its colorful light on a cabinet or shelf. Create beautiful accent lighting in any corner or wall even in narrow space.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Rectangle

## Design and finishing

- Color: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- On/off switch on wire: No
- Remote control included: No

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Functional
- EyeComfort: Yes

## Other characteristics

- Lamp current: 40 mA
- Efficacy: 72 lm/W

## Power consumption

- Power factor: 0.7
- Voltage: 220-240 V

## Product dimensions and weight

- Net weight: 0.35 kg
- Height: 4.2 cm
- Length: 30 cm
- Width: 4.5 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 25,000 hour(s)
- Total lumen output fixture: 400
- Light color: 2200-6500 (RGB)
- Fixture dimmable: Wireless Dim - Do not use with dimmer
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 5.5
- IP code: IP20
- Class of protection: Class II

## Packaging dimensions and weight

- EAN/UPC - product: 8719514435155
- Net weight: 0.35 kg
- Gross weight: 0.53 kg
- Height: 8.7 cm
- Length: 5.9 cm
- Width: 40.5 cm



Issue date: 2024-11-21  
Version: 0.86

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)