

PHILIPS

Braid Ceiling Light
24W


Ceiling Lights

6500K

White



8719514483637



High quality LED light designed to last for years

Philips Essential LED ceiling light brightens up your room in a soft and uniform light with long-lasting LED technology. Perfect for lighting up any general spaces like the balcony, kitchen and bathroom.

Easy to experience

- Easy installation

Light effect

- Bright light with uniform distribution

Durability

- Long life span up to 15,000 hours

Highlights

Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 225 mA
- Efficacy: 100 lm/W

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 0.56 kg
- Height: 7.6 cm
- Length: 38.5 cm
- Width: 38.5 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 385 mm
- Total lumen output fixture: 2400
- Light color: 6500
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- IP code: IP20
- Class of protection: Class I

8719514483637

Packaging dimensions and weight

- EAN/UPC - product: 8719514483637
- Net weight: 0.56 kg
- Gross weight: 1.18 kg
- Height: 45 cm
- Length: 9 cm
- Width: 44.5 cm



Issue date: 2024-11-21
Version: 0.93

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com