

PHILIPS

Ceiling light

Functional

CL210

White

8720169289468



High quality LED light designed to last for years

Philips Essential LED ceiling light brightens up your room in a soft and uniform light with long-lasting LED technology. Perfect for lighting up any general spaces like the balcony, kitchen and bathroom.

Designed for your living- and bedroom

- Perfect to relax and socialise

Safety

- LED protective cover for optimal light source insulation and ensure safety

Premium quality

- Premium faceted crystals for sparkling light effect

Highlights

Perfect to relax and socialise

The living room is the heart of any home - a place where families gather to relax and guests socialise. Lighting for your living- and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light

sources and playing with light layering helps create the feeling of space and to give the room a warm and welcoming feel.

LED protective cover for optimal light source insulation and ensure safety

Protects the LED itself to ensure it is protected when travelling and installing.

Premium faceted crystals for sparkling light effect

Faceted crystals a touch of refined, vintage charm to your space.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Number of switch cycles: 15,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Type: Ceiling Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 305 mA
- Efficacy: 117 lm/W

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 0.59 kg
- Height: 8 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 385 mm
- Total lumen output fixture: 4200
- Light color: 6500
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20
- Class of protection: Class I - Earthed

Packaging dimensions and weight

- EAN/UPC - product: 8720169289468
- Net weight: 0.59 kg
- Gross weight: 1.1 kg
- Height: 45 cm
- Length: 9 cm
- Width: 44.5 cm



Issue date: 2025-06-16
Version: 0.102

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com