

PHILIPS

Bulb 95W A60 B22

LED

6500K

1250lm

15000h

8718699747671



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

Highlights

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no

ultra-violet light means that fabric and items under this light won't fade.

Contains no mercury

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Type of glass: Frosted
- Dimmable: No
- Bulb Finish: Frosted

Bulb dimensions

- Height: 10.8 cm
- Width: 6 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 70
- Color temperature: 6500 K
- Nominal luminous flux: 1250 lm
- Warm-up time to 60% light: instant full light
- Color Code: 765 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 96 lm/W

Packaging information

- EAN: 8718699747671
- EOC: 871869974767100
- Product title: ESS LEDBulb 13W B22 6500K 230V 1CT/48 PK

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 13 W
- Wattage equivalent: 95 W

Product dimensions and weight

- Length: 10.8 cm

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699747671
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 10.6 cm
- Length: 6.1 cm
- Width: 6.1 cm



Issue date: 2024-11-21
Version: 0.27

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com