

PHILIPS

Filament Candle
Clear 20W B35 E14

LED

3000K

200lm

10000h

8718699623210



State-of-the-art LED light bulb for the home

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Highlights

Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional candle
- Socket: E14
- Dimmable: No
- Bulb Finish: Clear
- Bulb Material: Glass

Bulb dimensions

- Height: 9.7 cm
- Width: 3.5 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 10,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 200 lm

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 100 lm/W

Packaging information

- EAN: 8718699623210
- EOC: 871869962321000
- Product title: LEDClassic 2-20W B35 E14 830 CL NDAPR

Power consumption

- Power factor: 0.41
- Voltage: AC 220-240 V
- Wattage: 2 W
- Wattage equivalent: 20 W

Product dimensions and weight

- Length: 9.7 cm

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699623210
- Net weight: 0.02 kg
- Gross weight: 0.03 kg
- Height: 14.9 cm
- Length: 4 cm
- Width: 4 cm



Issue date: 2025-03-10
Version: 0.110

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com