

PHILIPS

Listra Wall Light 11W

Outdoor luminaires

3000K

Black

Water Resistant



046677582913



Create great outdoor moments

The Philips wall light illuminates and lightens up your entrance with diffused and warm white light.

Easy installation

- Easy installation

Sustainable light solutions

- Long lifetime up to 25,000 hours

Special characteristics

- Powerful light

Highlights

Easy installation



Installing a luminaire can be sometimes difficult. With this Philips luminaire, you can be sure that high attention has been given to facilitate it and simplify it for you. You'll find clear guidance about where you can install the product and relevant information about water-resistant IP ratings.

Long lifetime up to 25,000 hours



Reliable high-quality LED light lasts up to 25,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

Powerful light



This Philips outdoor luminaire provides powerful light. A bright pool of light to light up your garden or terrace.

Specifications

Design and finishing

- Color: Black
- Material: Aluminium

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- 5 years warranty on the LED module: Yes
- Anti rust anti dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Warm White Light: No
- Centerpiece: No

Garden area

- Garden area: Garden & Patio

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 1.65 kg
- Height: 35.5 cm
- Length: 20.6 cm
- Width: 16 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Total lumen output fixture: 650
- Light color: 3000
- Mains power: 120 V
- Energy class included light source: not applicable
- IP code: UL03 - Wet Location (North America)
- Class of protection: Class I

- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC - product: 046677582913
- Net weight: 1.65 kg
- Gross weight: 1.86 kg
- Height: 41 cm
- Length: 18 cm
- Width: 23 cm



Issue date: 2025-02-02
Version: 0.96

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com