

PHILIPS

Reflector 120W
PAR38 E26

LED

2700K

1200lm

15000h

046677585440



Smart lighting for you daily living

PAR38 with daylight and motion sensor to provide an easy smart lighting for you

Light beyond illumination

- Instant on
- Built-in automatic on/off light sensor

Highlights

Instant on Day and night sensor



With its built-in automatic light sensor, this bulb switches on automatically after dusk and off after dawn.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Glass

Bulb dimensions

- Height: 13.7 cm
- Width: 12.2 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 1200 lm

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 92 lm/W

Packaging information

- EAN: 046677585440
- EOC: 585448
- Product title: 13PAR38/S/120W/927 40D ND/G/110-277V/T20

Power consumption

- Power factor: 0.7
- Voltage: AC 110-277 V
- Wattage: 13 W
- Wattage equivalent: 120 W

Product dimensions and weight

- Length: 13.7 cm

Rated values

- Rated peak intensity: 2231 cd

Technical specifications

- Frequency: 50-60 Hz

046677585440

Packaging dimensions and weight

- EAN/UPC - product: 046677585440
- Net weight: 0.31 kg
- Gross weight: 0.34 kg
- Height: 18 cm
- Length: 13.1 cm
- Width: 13.1 cm
- Material number (12NC): 929003700503



Issue date: 2024-09-17
Version: 0.89

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com