

DESCRIPTION

Adjustable square gimbal trim designed for use with IC or Non-IC AIR-TITE™ 3" Halo small aperture line and low voltage housings. This die-cast aluminum trim is available in multiple finishes to match interior decor. Trim uses low voltage MR16 or GU10 line voltage lamps ideal for accent and task lighting. Trim offers 35° positive tilt, 15° negative tilt, and 360° orientation within housing. The trim construction allows use with the Halo H3 Series of standard round aperture housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Adjustable square gimbal trim available in Matte White, Black, Satin Nickel, or Tuscan Bronze finishes. Lamp replacement is via snap-in front loading plate. Three pressure springs ensure positive retention in housing.

Trim includes cover glass lens which may be replaced with a variety of media. (Lamps that have integral glass lens do not require use of the cover glass supplied with this trim).

3013 is designed for use with the following Halo H3 (standard round) small aperture housings:


- Line Voltage Housing (for 120V GU10 lamps).

H36ICAT	50W	IC Air-Tite Housing
H36TAT	50W	Non-IC Air-Tite Housing
H36RTAT	50W	Non-IC Air-Tite Remodel Housing
- LowVoltage Housing (for 12V MR16 lamps).

H36LVICAT	50W	IC Air-Tite Housing
H36LVTAT	50W	Non-IC Air-Tite Housing
H36LVRTAT	50W	Non-IC Air-Tite Remodel Housing
H36LVTAT277	50W	Non-IC Air-Tite Housing, 120/277V
H36LVRTAT277	50W	Non-IC Air-Tite Remodel Housing, 120/277V
- Line Voltage Housing (for 120V GU10 lamps).

H38ICAT	50W	IC Air-Tite Housing
---------	-----	---------------------
- LowVoltage Housing (for 12V MR16 lamps).

H38LVICAT	37W	IC Air-Tite Housing
-----------	-----	---------------------



Lamp Aperture	2" [51mm]
Gimbal:	2-1/4" [57mm]
Ceiling Opening (round):	3-3/4" [95mm]
Outside Diameter:	4-1/4" Square [108mm]



3013WH
White



3013BK
Black



3013SN
Satin Nickel



3013TBZ
Tuscan Bronze

3013

3" Adjustable Gimbal Square Trim

3" TRIMS

ORDERING INFORMATION

SAMPLE NUMBER: 3013WH

Order housing and trims separately.

Trim	Finish
3013= 3" Adjustable Gimbal Square Trim	WH =White BK =Black SN =Satin Nickel TBZ =Tuscan Bronze