

E26 6" Trim Series


DESCRIPTION

Air-Tite™ baffle trim with reflector 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

| | | |
|-------------|--|------|
| Catalog # | | Type |
| Project | | |
| Comments | | Date |
| Prepared by | | |

SPECIFICATION FEATURES

- Self-flange metal baffle with upper reflector
- Socket supporting baffle
- Torsion spring retention
- Accepts a wide range of lamps
- Makes installation Air-Tite regardless of housing used



Dimensions:

H: 5" [127mm]

OD: 7-1/4" [184mm]

| Housings | Max Lamp Compatibility |
|------------------|---|
| H7ICT H7ICAT | 40W A19, 75W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40, 75W R30 |
| H7RICT H7RICAT | 30WAT, 30WATH, 30PAT: 40W A19, 75W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40 |
| E7ICAT E7RICAT | 30SNAT, 30TBZAT: 40W A19, 60W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40 |
| H7UICAT | 70W A19, 75W PAR30S, 75W PAR30L, 100W PAR38, 85W BR30, 100W R30 |
| H7ICTNB H7ICATNB | 40W A19, 75W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40, 75W R30 |
| E7ICATNB | 30WAT, 30WATH, 30PAT: 40W A19, 75W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40 30SNAT, 30TBZAT: 40W A19, 60W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40 |
| H7T | 100W A19, 150W A21, 75W PAR30S, 75W PAR30L, 150W PAR38, 85W BR30, 100W R30 |
| H7TCP | 75W A19, 75W PAR30S, 75W PAR30L, 150W PAR38, 85W BR30, 100W R30 |
| H7RT | 100W A19, 150W A21, 50W PAR30S, 50W PAR30L, 150W PAR38, 85W BR30, 100W R30 |
| E7TAT | 100W A19, 150W A21, 75W PAR30S, 75W PAR30L, 150W PAR38, 65W BR30 |
| E7RTAT | 100W A19, 150W A21, 50W PAR30S, 75W PAR30L, 150W PAR38, 65W BR30 |
| H7TNB | 100W A19, 150W A21, 75W PAR30S, 75W PAR30L, 150W PAR38, 85W BR30, 100W R30 |
| E7TATNB | 100W A19, 150W A21, 75W PAR30S, 75W PAR30L, 150W PAR38, 65W BR30 |

Compatible with Halogen, Incandescent, LED* or CFL* lamps.

ORDERING INFORMATION

SAMPLE NUMBER: 30WAT

| Trim | Finish |
|--|-------------------|
| 30WAT= 6" White Baffle & Reflector, White Trim | WH=White |
| 30WATH= 6" White Baffle & Clear Reflector, White Trim | WH=White |
| 30PAT= 6" Black Baffle & Reflector, White Trim | WH=White |
| 30SNAT= 6" Satin Nickel Baffle & Reflector, Satin Nickel Trim | SN=Satin Nickel |
| 30TBZAT= 6" Tuscan Bronze Baffle & Reflector, Tuscan Bronze Trim | TBZ=Tuscan Bronze |

HALO HOUSING COMPATIBILITY

| Trim # | Style | H7ICT | H7ICAT | H7RICT | H7RICAT | E7ICAT | E7RICAT | H7UICAT | H7ICTNB |
|---|--------------------|----------|----------|---------|----------|---------|----------|---------|---------|
| 30WAT 30WATH 30PAT 30SNAT 30TBZAT | Reflector & Baffle | • | • | • | • | • | • | • | • |
| | | H7ICATNB | E7ICATNB | H27ICAT | H27RICAT | E27ICAT | E27RICAT | | |
| | | • | • | | | | | | |
| | | H7T | H7TCP | H7RT | E7TAT | E7RTAT | H7TNB | E7TATNB | H27T |
| • | • | • | • | • | • | • | • | | |
| | | H27RT | E27TAT | E27RTAT | | | | | |
| | | | | | | | | | |

For use in select other's housings, refer to U.L. classification list at www.cooperlighting.com.

*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Cooper Lighting Solutions does not warranty the lamp.



30WAT
White Trim, White Baffle and Reflector




30WATH
White Trim, White Baffle and Clear Reflector



30PAT
White Trim, Black Baffle and Clear Reflector



30SNAT
Satin Nickel Trim, Satin Nickel Baffle and Reflector



30TBZAT
Tuscan Bronze Trim, Tuscan Bronze Baffle and Reflector

30

6-Inch Super Trim™
Air-Tite™ Baffle



For use in Halo listed housings.



Select trims are classified for use in others housings.
See www.cooperlighting.com.

TD518201EN
10/19/2016