



CorePro Plastic LED-spesialiteter



Corepro LED T25 ND 1.7-15W E14 827

LED-spesialitetene kan enkelt monteres i visse bruksområder.

Produktdata

Generell informasjon	
Sokkelbase	E14 [E14]
Nominell levetid	15 000 time(r)
Brytersyklus	50 000
Lighting Technology	LED
I samsvar med EU RoHS	Ja
Teknisk belysning	
Fargekode	827 [CCT of 2700K]
Spredningsvinkel (nom.)	240 grad(er)
Lysytelse	150 lm
Fargebetegnelse	Varmhvit (WW)
Korrelert fargetemperatur (nom)	2700 K
Lysutbytte (vurdert) (Nom)	88,00 lm/W
Fargesamsvar	<6
Fargegjengivelsesindeks (CRI)	80
Nominell vedlikeholdsfaktor for lyskildelumen ved utgangen av nominell levetid (nom.)	70 %
Flimmerverdi (PstLM)	1
Stroboskopisk effekt	0,4
Photobiological safety according to EN 62471	RGO

Drift og elektronikk	
Line Frequency	50 to 60 Hz
Inngangsfrekvens	50 til 60 Hz
Effektforbruk	1,7 W
lyskildestrom (nom.)	20 mA
Effekten som tilsvare	15 W
Starttid (nom.)	0,5 s
Tiden det tar før lyset er på 60 %	0,5 s
Effektfaktor (brøk)	0,4
Spenning (nom.)	220-240 V

Temperatur	
Maksimal temperatur for innfatningen (nom.)	55 °C

Kontroller og dimming	
Kan dimmes	Nei

Mekanikk og innfatning	
Lyspæreoverflate	Matt
Lyspæreform	T25 [T 25 mm]


Godkjenning og bruksområde	
Energieffektivitetsklasse	F

CorePro Plastic LED-spesialiteter

Energiforbruk kWh/1000 t	2 kWh
EPREL-registreringsnummer	391879
EyeComfort	Ja
Produktdata	
Produktnavn for bestilling	Corepro LED T25 ND 1.7-15W E14 827
Fullstendig produktnavn	Corepro LED T25 ND 1.7-15W E14 827
Full EOC	871951438986100
Lokal kodebeskrivelse	3767099



Bestillingskode	38986100
Materialenr. (12NC)	929001325702
Lokal bestillingskode	3767099
SAP-teller – antall per pakke	1
EAN/UPC – produkt/boks	8719514389861
SAP-teller – pakker per utvendige	12
EAN/UPC – boks	8719514389878

Målskisse




Product	D	C
Corepro LED T25 ND 1.7-15W E14 827	25 mm	59 mm

Fotometriske data



Light Distribution Diagram - Corepro LED T25 ND 1.7-15W E14 827



General uniform lighting - Corepro LED T25 ND 1.7-15W E14 827



Spectral Power Distribution Colour - Corepro LED T25 ND 1.7-15W E14 827

CorePro Plastic LED-spesialiteter

Levetid



Life Expectancy Diagram - Corepro LED T25 ND 1.7-15W E14 827

Lumen Maintenance Diagram - Corepro LED T25 ND 1.7-15W E14 827

