



# CorePro LEDcapsule MV



## CorePro LEDcapsule 2-25W ND G9 827

The LED specialties deliver a high quality light to make themselves to be a true replacement of halogen specialty lamp (such as G9 and R7S). It is particularly suit for task lighting in hotel and restaurants, and ideal for decorative and ambient application. LEDspecialty products deliver huge energy saving and minimize maintenance costs, without any compromise on light quality.

### Product data

General Information	
Cap-Base	G9
Nominal lifetime	15,000 hour(s)
Switching Cycle	8,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	220 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	110.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM) - Flickering value as per 1 EN 61000-3-3	

Stroboscopic effect visibility measure (SVM)	0.4
Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	2 W
Lamp Current (Nom)	20 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	78 °C
Controls and Dimming	
Dimmable	No

# CorePro LEDcapsule MV

## Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	Capsule

## Approval and Application

Energy Efficiency Class	E
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
EPREL Registration Number	453187
EyeComfort	Yes


## Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

## Product Data



Order product name	CorePro LEDcapsule 2-25W ND G9 827
Full product name	CorePro LEDcapsule 2-25W ND G9 827
Full product code	871951430389800
Order code	929002495202
Material Nr. (12NC)	929002495202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514303898
Numerator - Packs per outer box	12
EAN/UPC - Case	8719514303904

## Dimensional drawing



Product	D	C
CorePro LEDcapsule 2-25W ND G9 827	14.5 mm	48 mm

## Photometric data




Light Distribution Diagram - CorePro LEDcapsule 2-25W ND G9 827

General uniform lighting - CorePro LEDcapsule 2-25W ND G9 827

# CorePro LEDcapsule MV

## Photometric data



Spectral Power Distribution Colour - CorePro LEDcapsule 2-25W ND G9 827

## Lifetime



Life Expectancy Diagram - CorePro LEDcapsule 2-25W ND G9 827



Lumen Maintenance Diagram - CorePro LEDcapsule 2-25W ND G9 827

