



CorePro LEDcapsule MV



CorePro LEDcapsule 2-25W ND G9 830

The LED specialties deliver a high quality light to make themselves to be a true replacement of halogen specialty lamp (such as G9 and R7S). It is particularly suit for task lighting in hotel and restaurants, and ideal for decorative and ambient application. LEDspecialty products deliver huge energy saving and minimize maintenance costs, without any compromise on light quality.

Product data

General Information	
Cap-Base	G9
Nominal lifetime	15,000 hour(s)
Switching Cycle	8,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	220 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	110.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

Stroboscopic effect visibility measure (SVM)	0.4
Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	2 W
Lamp Current (Nom)	20 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	78 °C
Controls and Dimming	
Dimmable	No

CorePro LEDcapsule MV

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	Capsule

Approval and Application

Energy Efficiency Class	E
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
EPREL Registration Number	453188
EyeComfort	Yes


Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

Product Data



Order product name	CorePro LEDcapsule 2-25W ND G9 830
Full product name	CorePro LEDcapsule 2-25W ND G9 830
Full product code	871951430391100
Order code	929002495302
Material Nr. (12NC)	929002495302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514303911
Numerator - Packs per outer box	12
EAN/UPC - Case	8719514303928

Dimensional drawing



Product	D	C
CorePro LEDcapsule 2-25W ND G9 830	14.5 mm	48 mm

Photometric data




General uniform lighting - CorePro LEDcapsule 2-25W ND G9 830

Light Distribution Diagram - CorePro LEDcapsule 2-25W ND G9 830

CorePro LEDcapsule MV

Photometric data



Spectral Power Distribution Colour - CorePro LEDcapsule 2-25W ND G9 830

Lifetime



Life Expectancy Diagram - CorePro LEDcapsule 2-25W ND G9 830



Lumen Maintenance Diagram - CorePro LEDcapsule 2-25W ND G9 830

