



# Contractor-grade Plastic (Non-Dimmable) A-Shape Lamps

12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB

Most affordable A19 lamp ideal for residential, back of house closets.

## Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	11,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	250 degree(s)
Luminous Flux	1,100 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	12.2 W
Lamp Current (Nom)	98 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	185 °F
Controls and Dimming	
Dimmable	No

# Contractor-grade Plastic (Non-Dimmable) A-Shape Lamps

## Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19

## Approval and Application


Energy Certifications	No
-----------------------	----

## Product Data

Order product name	12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB
--------------------	---------------------------------------



Full product name	12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB
Order code	571653
Material Nr. (12NC)	929003020604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677571658
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677571653

## Dimensional drawing



Product	D	C
12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB	2-3/8 inch	4-5/8 inch

## Photometric data




General uniform lighting - 12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB

Light Distribution Diagram - 12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB


# Contractor-grade Plastic (Non-Dimmable) A-Shape Lamps

## Photometric data




Spectral Power Distribution Colour - 12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB

## Lifetime



Lumen Maintenance Diagram - 12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB



Life Expectancy Diagram - 12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB

