



# TUV PL-L - Compact solution for professional applications

## TUV PL-L

TUV PL-L lamps are compact UVC (germicidal) lamps used in professional water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-L lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

### Benefits

- Security of effective disinfection over the useful lifetime of the lamp
- High system efficacy because it is not required to over-design the purification system to maintain effectiveness of disinfection

### Features

- Short-wave UV radiation with a peak at 253.7 nm (UVC) for disinfection purposes
- Protective inside coating ensures constant UV output over the complete lifetime of the lamp
- Special lamp glass filters out the 185 nm ozone-forming radiation
- High Output versions contain wind-chill correction for improved performance in moving air and reducing amount of required lamps
- High Output versions for optimum UVC output per lamp length, allowing for reduction of system size
- Warning sign on lamp indicates that the lamp radiates UVC

## Application

- Deactivation of bacteria, viruses and other micro-organisms
- Residential drinking water units
- Fish pond and process water units
- In-duct air treatment units
- Stand alone air purifiers
- Air disinfection systems in for example hospitals, universities and laboratories

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

## Versions



TUV PL-L

## Dimensional drawing

Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-L 55W/4P HF 1CT/25	18 mm	38 mm	505 mm	530 mm	535 mm
TUV PL-L 36W/4P 1CT/25	18 mm	38 mm	385 mm	410 mm	415 mm
TUV PL-L 95W/4P HO 1CT/25	18 mm	38 mm	505 mm	530 mm	535 mm
TUV PL-L 18W/4P 1CT/25	18 mm	39 mm	195 mm	220 mm	225 mm
TUV PL-L 24W/4P UNP/50	18 mm	39 mm	290 mm	315 mm	320 mm
TUV PL-L 60W/4P HO 1CT/25	18 mm	38 mm	390 mm	415 mm	420 mm
TUV PL-L 35W/4P HO 1CT/25	18 mm	39 mm	195 mm	220 mm	225 mm

General Information	
Cap-Base	2G11
Useful Life (Nom)	9000 h
Main Application	Disinfection
Light Technical	
Color Code	TUV
Color Designation	-
Lumen Depreciation At Useful Lifetime	15 %
Mechanical and Housing	
Bulb Shape	2xT16

## Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
210641	TUV PL-L 18W 25PK	4.4 mg
151271	TUV PL-L 24W/4P UNP/50	4.4 mg
265850	TUV PL-L 36W 25PK	-
137265	PL-L 35W/TUV 25PK	4.4 mg

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
294645	TUV 55W PLL 25PK	4.4 mg
130351	TUV PL-L60W	4.4 mg
137257	TUV PL-L 95W HO 25PK	4.4 mg

## Operating and Electrical

Order Code	Full Product Name	Lamp Current		Power (Rated)
		(Nom)	Voltage (Nom)	(Nom)
210641	TUV PL-L 18W 25PK	0.37 A	60 V	18 W
151271	TUV PL-L 24W/4P UNP/50	0.345 A	87 V	24 W
265850	TUV PL-L 36W 25PK	0.44 A	105 V	36 W

Order Code	Full Product Name	Lamp Current		Power (Rated)
		(Nom)	Voltage (Nom)	(Nom)
137265	PL-L 35W/TUV 25PK	0.85 A	42 V	35 W
294645	TUV 55W PLL 25PK	0.54 A	103 V	55 W
130351	TUV PL-L60W	0.800 A	84 V	60 W
137257	TUV PL-L 95W HO 25PK	0.8 A	115 V	90 W

## General Information

Order Code	Full Product Name	System Description
210641	TUV PL-L 18W 25PK	na
151271	TUV PL-L 24W/4P UNP/50	na
265850	TUV PL-L 36W 25PK	na
137265	PL-L 35W/TUV 25PK	na

Order Code	Full Product Name	System Description
294645	TUV 55W PLL 25PK	High Frequency
130351	TUV PL-L60W	na
137257	TUV PL-L 95W HO 25PK	High Frequency

## UV

Order Code	Full Product Name	UV-C Radiation
210641	TUV PL-L 18W 25PK	5.5 W
151271	TUV PL-L 24W/4P UNP/50	7.1 W
265850	TUV PL-L 36W 25PK	12.0 W
137265	PL-L 35W/TUV 25PK	11.0 W

Order Code	Full Product Name	UV-C Radiation
294645	TUV 55W PLL 25PK	17.0 W
130351	TUV PL-L60W	19.0 W
137257	TUV PL-L 95W HO 25PK	27.0 W

