



GreenPerform Highbay Elite

BY718P LED300/NW PSD NB

GreenPerform Highbay Elite, 217 W, 32500 lm, 4000 K, DALI, 54°

GreenPerform Highbay Elite is the latest innovation in a successful range of highbay luminaires for high ceiling and industrial applications. The unique finless design has received the iF Design Award 2019 and Reddot Design Award 2019 for its aesthetic appeal. But this versatile luminaire offers a wealth of practical features too, including great light quality, high energy savings, a long lifetime at an affordable price and a wide variety of optics and lumen packages. The Green Perform Highbay Elite luminaire provides options for advanced connectivity with IoT based systems and software applications including the Interact Pro system. If you're looking for a "fit and forget" robust and reliable solution with connectivity advantages, Green Perform Highbay Elite is the smart choice.

Product data

General Information		EU RoHS compliant	
Light source replaceable	No		Yes
Number of gear units	2 units	Light Technical	
Driver included	Yes	Luminous Flux	32,500 lm
Light source engine type	LED	Correlated Color Temperature (Nom)	4000 K
Service tag	Yes	Luminous Efficacy (rated) (Nom)	150 lm/W
CE mark	CE mark	Color rendering index (CRI)	>80
Warranty period	3 years	Light source color	840 neutral white
Flammability mark	For mounting on normally flammable surfaces	Optic type	Symmetrical
ENEC mark	-	Optical cover type	Polycarbonate bowl/cover
Glow-wire test	Temperature 650 °C, duration 30 s	Luminaire light beam spread	54°

GreenPerform Highbay Elite

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	122 A
Inrush time	0.2 ms
Power Consumption	217 W
Power Factor (Fraction)	0.95
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B	6

Temperature

Ambient temperature range	-30 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Black and gray
Optical cover finish	Frosted
Overall height	464 mm
Overall diameter	510 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.0042 %
Median useful life L70B50	75,000 hour(s)


Application Conditions

Maximum dim level	1%
Suitable for random switching	No

Product Data

Order product name	BY718P LED300/NW PSD NB
Full product name	BY718P LED300/NW PSD NB
Full product code	872016954873200
Order code	911401581551
Material Nr. (12NC)	911401581551
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169548732
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169548732

Dimensional drawing



GreenPerform Highbay Elite

